

SPEC SHEET + MEASUREMENTS

SPORT-TEK

Sport-Tek® PosiCharge® Reversible Mesh Tank. ST5000

Product photo



Perform at your peak in a moisture-wicking, open-holed mesh tank with PosiCharge technology which locks in logos and colors.

- 3.4-ounce, 100% open-holed poly mesh with PosiCharge technology
- Moisture-wicking
- Reversible mesh
- Double-layer construction with open, individually hemmed layers for easy decoration inside and out
- Tear-away label

CARE INSTRUCTIONS

Machine Wash Cold With Like Colors. Do Not Use Fabric Softener. Do Not Bleach. Tumble Dry Low. Remove Promptly. Cool Iron, If Necessary.

Sketches



front



back

SPEC SHEET + MEASUREMENTS

SPORT-TEK

Sport-Tek® PosiCharge® Reversible Mesh Tank. ST5000

PRODUCT MEASUREMENTS

| | XS | S | M | L | XL | 2XL | 3XL | 4XL |
|---------------------|--------|--------|--------|--------|--------|--------|--------|--------|
| Body Length at Back | 27 1/2 | 28 1/2 | 29 1/2 | 30 1/2 | 31 1/2 | 32 1/2 | 33 | 33 1/2 |
| Chest | 18 | 19 1/2 | 21 | 22 1/2 | 24 | 25 1/2 | 27 1/2 | 29 1/2 |


Body Length at Back: Measured from high point shoulder to finished hem at back.

Chest: Measured across the chest one inch below armhole when laid flat.

SIZE CHARTS

| | XS | S | M | L | XL | 2XL | 3XL | 4XL |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| Chest | 32-34 | 35-37 | 38-40 | 41-43 | 44-46 | 47-49 | 50-53 | 54-57 |

HOW TO MEASURE



CHEST

Measure under the arm and around the fullest part of the chest with arms down, keeping tape horizontal.

SPEC SHEET + MEASUREMENTS



Sport-Tek® PosiCharge® Reversible Mesh Tank. ST5000

COLORS



Black/ Deep Red
PMS BLACK C



Black/ White
PMS BLACK C



Carolina Blue/ White
PMS 646C



Deep Orange/ White
PMS 173C



Deep Red/ White
PMS 201C



Forest Green/ White
PMS 553C



Gold/ Black
PMS 1235C



Iron Grey/ White
PMS 7540C



Kelly Green/ White
PMS 341C



Maroon/ White
PMS 504C



Purple/ White
PMS 7672C



True Navy/ White



True Royal/ White
PMS 7687C



Vegas Gold/ Black
PMS 4525C